

J.P.
EXPORT · IMPORT

SLIT LAMP

Henvar

H-2000



SCIENTIFICS INSTRUMENTS

SPECIFICATIONS AND FEATURES

It is desing especially for contactology

MICROSCOPE

Type	Binocular stereo-microscope
Magnifications chaiging system	Revolver type objetive chaniging system for making two magnifications changes
Objetives	1 x and 1.6 x
Eypieces	10 x
Magnifications:	
Objective x Eypieces = Magnification	
1 x 10 x	10 x
1.6 x 10 x	16 x
Dioptric adjustements	
Eypiece 10 x	± 8 Diopters for both eyes
Angle of optical axes	13°
Range of pupillary distance (P.D.)	54-94 mm

SLIT LAMP

Slit illuminated field	
Slit width	Continuously variable from 0 to 10 mm
Slit lenth	Continuously variable from 8 to 1 mm (comet system)
Aperture diaphragms	10 mm, 9 mm, 5 mm, 3 mm, 2 mm, 1 mm and 0,2 mm
Slit angle	Continuously variable through 90 ° from vertical to the horinzontal; horizontal scanning is possible
Filters	Open, cobalt blue, yellow, green and anticaloric
Lamp	Incandescent precentered bulb to 6 V, 27 W. Also available lamp halogenous of 12 V, 35 W, both brightness continously adjustable

BASE

Longitudinal movement	100 mm
Lateral movement	95 mm
Fine adjustment	± 10 mm in both direcctions
Vertical movement	30 mm

CHIN-REST

Vertical movement	80 mm maximun
-------------------	---------------

POWER

Input (primary)	CA 110 V; 125 V; 220 V and 240 V (50/60 Hz) adjustable with voltaje selector
Output (secondary)	Adjustable potentiometer 0 ÷ 6 V AC. Also available 0 ÷ 12 V AC for halogenous bulb

ACCESORIES

4 Screw head star (M3x18) with it nuts	2 Pack of chinrest pads
2 Tracks covers	1 Cover
2 Wide mirrors	2 Allen wrenches 5 and 6 mm
1 Testing rod	1 Power cord
1 Cap for testing rod hole	1 Fuse 0,3 A
1 Sanatory protection cap	1 Incandescent bulb 6 V, 4.5 A or
1 Chinrest tissue pins	Halogenous bulb of 12 V


SPARE ITEMS

SPARE ITEMS	FEATURES	BOBES CODES (For supplied)
Net conector	With fuse support	170300
Illumination lamp	(6 V, 27 W); (12 V, 35 W)	170505; 170502
Intensity lamp	PCI + components	170839
Transforming	110/120/220/240 V	170554

More substitutive components (it can be supplied by BOBES, S.A.):

SPARE ITMES	FEATURES	BOBES CODES (For supplied)
Wire with net conector	220 V, Dowll Schuck	170066
Wire with net conector	110 V, Hospital Grade	170065
Fuses	Slow. 220 V-240 V AC 315 mA / 250 V. Diameter 5x20	170179
Fuses	Slow. 110 V-120 V AC 2 mA / 250 V. Diameter 5x20	170180

Company registered in F.D.A. (U.S.A.). Instrument according regulations UNE EN 60601-1; UL2601-1;CAN/CSA C22.2 N.º 601.1



J.P. Export - Import S.L.
info@jpbobes.com

J.P.
EXPORT · IMPORT

Avenida de España, 51 El Molar 28710 Madrid
Tlf./Fax: 91 841 08 81

Desingn and especifications could be subject to changes without warning

